Pushing Performance
Since 1945

HPP V4 Power crimp contact male 1,5mm²



Image is for illustration purposes only. Please refer to product description.

Part number	09 46 500 0401
Specification	HPP V4 Power crimp contact male 1,5mm²
HARTING eCatalogue	https://harting.com/09465000401

Identification

Category	Contacts
Series	HARTING PushPull (V4)
Type of contact	Crimp contact

Version

Termination method	Crimp termination
Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section (mm²)	1.5 mm²
Conductor cross-section (AWG)	AWG 16 ... AWG 14
Mating cycles	≥750

Material properties

Material (contacts)	Copper alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Lead
ECHA SCIP number	339476a1-86ba-49e9-ab4b-cd336420d72a
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Commercial data

Packaging size	100
Net weight	0.46 g
Country of origin	Switzerland
European customs tariff number	85366990
GTIN	5713140065444
eCl@ss	27440204 Contact for industrial connectors
ETIM	EC000796
UNSPSC 24.0	39121522

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.