


Split Loom

Features

- Designed to Hold and Protect Cables, Harnesses, and Hoses
- Quick and Easy to Install. Slit Automatically Closes after Installation
- .013 Heavy Duty Wall Thickness Provides Greater Resistance to Abrasions and Vibrations
- Polyethylene Construction
- Temperature Rating:
+85°C (+185°F) Continuous Rating for 3000 Hours
+115°C (+239°F) Short Term Rating for 168 Hours

SL-01



Black Split Loom



NTE Type No.	Feet per Roll	Inner Diameter (in. / mm)	Outer Diameter (in. / mm)	Wall Thickness (in. / mm)	Diag No.
04-SLPE2500	100	.288 / 7.31	.390 / 9.90	.013 / .330	SL-01
04-SLPE2500-10	10	.288 / 7.31	.390 / 9.90	.013 / .330	SL-01
04-SLPE2500-5	5	.288 / 7.31	.390 / 9.90	.013 / .330	SL-01
04-SLPE2500A	25	.288 / 7.31	.390 / 9.90	.013 / .330	SL-01
04-SLPE3750	100	.415 / 10.54	.532 / 13.51	.013 / .330	SL-01
04-SLPE3750-10	10	.415 / 10.54	.532 / 13.51	.013 / .330	SL-01
04-SLPE3750-5	5	.415 / 10.54	.532 / 13.51	.013 / .330	SL-01
04-SLPE3750A	25	.415 / 10.54	.532 / 13.51	.013 / .330	SL-01
04-SLPE3750B	1800	.415 / 10.54	.532 / 13.51	.013 / .330	SL-01
04-SLPE5000	100	.511 / 12.97	.660 / 16.76	.013 / .330	SL-01
04-SLPE5000-10	10	.511 / 12.97	.660 / 16.76	.013 / .330	SL-01
04-SLPE5000-5	5	.511 / 12.97	.660 / 16.76	.013 / .330	SL-01
04-SLPE5000A	25	.511 / 12.97	.660 / 16.76	.013 / .330	SL-01
04-SLPE6250	100	.663 / 16.84	.806 / 20.47	.013 / .330	SL-01
04-SLPE6250-10	10	.663 / 16.84	.806 / 20.47	.013 / .330	SL-01
04-SLPE6250-5	5	.663 / 16.84	.806 / 20.47	.013 / .330	SL-01
04-SLPE6250A	25	.663 / 16.84	.806 / 20.47	.013 / .330	SL-01
04-SLPE6250B	900	.663 / 16.84	.806 / 20.47	.013 / .330	SL-01
04-SLPE7500	100	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE7500-5	5	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE7500-10	10	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE7500A	25	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE7500B	600	.790 / 20.06	.928 / 23.57	.013 / .330	SL-01
04-SLPE10000	100	.917 / 23.29	1.073 / 27.25	.013 / .330	SL-01
04-SLPE10000-5	5	.917 / 23.29	1.073 / 27.25	.013 / .330	SL-01
04-SLPE10000A	25	.917 / 23.29	1.073 / 27.25	.013 / .330	SL-01
04-SLPE12500-5	5	1.295 / 32.89	1.500 / 38.10	.013 / .330	SL-01
04-SLPE12500A	25	1.295 / 32.89	1.500 / 38.10	.013 / .330	SL-01
04-SLPE12500B	100	1.295 / 32.89	1.500 / 38.10	.013 / .330	SL-01
04-SLPE15000-5	5	1.468 / 37.21	1.734 / 44.04	.013 / .330	SL-01
04-SLPE15000A	25	1.468 / 37.21	1.734 / 44.04	.013 / .330	SL-01
04-SLPE15000	100	1.468 / 37.21	1.734 / 44.04	.013 / .330	SL-01

Colored Split Loom

Features

- Designed to Hold and Protect Cables, Harnesses, and Hoses
- Quick and Easy to Install. Slit Automatically Closes after Installation
- Polyethylene Construction
- Temperature Rating:
 Brittleness Temperature (ASTM D746): -50°C (-58°F)
 Vicat Softening Temperature (ASTM D1525): +87°C (+188°F)

SL-01



Colored Split Loom (Note 1)

NTE Type No.	Length (feet)	Inner Diameter (in. / mm)	Outer Diameter (in. / mm)	Max. Wall Thickness (in. / mm)	Diag No.
04-SL.250-X	100	.266 / 6.75	.395 / 9.92	.010 / .254	SL-01
04-SL.250-X-5	5	.266 / 6.75	.395 / 9.92	.010 / .254	SL-01
04-SL.250-X-10	10	.266 / 6.75	.395 / 9.92	.010 / .254	SL-01
04-SL.375-X	100	.419 / 10.64	.535 / 13.59	.008 / .203	SL-01
04-SL.375-X-5	5	.419 / 10.64	.535 / 13.59	.008 / .203	SL-01
04-SL.375-X-10	10	.419 / 10.64	.535 / 13.59	.008 / .203	SL-01
04-SL.500-X	100	.505 / 12.83	.670 / 17.02	.010 / .254	SL-01
04-SL.500-X-5	5	.505 / 12.83	.670 / 17.02	.010 / .254	SL-01
04-SL.500-X-10	10	.505 / 12.83	.670 / 17.02	.010 / .254	SL-01
04-SL.625-X	100	.650 / 16.51	.825 / 20.96	.008 / .203	SL-01
04-SL.625-X-5	5	.650 / 16.51	.825 / 20.96	.008 / .203	SL-01
04-SL.625-X-10	10	.650 / 16.51	.825 / 20.96	.008 / .203	SL-01
04-SL.750-X	100	.761 / 19.33	.927 / 23.55	.008 / .203	SL-01
04-SL.750-X-5	5	.761 / 19.33	.927 / 23.55	.008 / .203	SL-01
04-SL.750-X-10	10	.761 / 19.33	.927 / 23.55	.008 / .203	SL-01
04-SL1.00-X	100	.909 / 23.09	1.033 / 26.24	.010 / .254	SL-01
04-SL1.00-X-5	5	.909 / 23.09	1.033 / 26.24	.010 / .254	SL-01
04-SL1.00-X-10	10	.909 / 23.09	1.033 / 26.24	.010 / .254	SL-01

Note 1. Replace "X" in device number with O = Orange, G = Green, R = Red, Y = Yellow, W = White.