

YF2206ID

Elect Cu Single Insul Wire Ferrules, Smooth Funnel Entry, 22 AWG, 0.47" L, Tin Plated, White

[Image](#) | [Line Art](#) | [3D Model](#) | [Video](#) | [Customer Drawing](#)

 [Email Datasheet](#)

 [Print Datasheet](#)

Specifications

Documents

Tools & Dies

Dimensional

General

Conductor(s)

Physical

Approvals / Certifications

Other Features

Dimensional	
D2 (in)	0.10
D - in	0.05
D1 (in)	0.04
L1 (in)	0.47
Total Length	0.24
General	
Number of Conductors	1
Product Description	Elect Cu Single Insul Wire Ferrules, Smooth Funnel Entry, 22 AWG, 0.47" L, Tin Plated, White
Conductor(s)	
Copper Stranded (Range)	22 AWG
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Plated (Yes or No)	Y
Product Material	Copper
Insulated (Yes or No)	Y
Approvals / Certifications	
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Other Features	
UPC	7818104833677

Active

