

## 6-Outlet Commercial-Grade Surge Protector, 6 ft. (1.83 m) Cord, 900 Joules, 12.5-in. length

MODEL NUMBER: PM6SN1



### Highlights

- 6 outlets/6-ft. (1.83 m) cord
- 900 joule rating

### Package Includes

- PM6SN1 Power Strip
- Warranty information
- Instruction manual

### Description

The PM6SN1 Power Strip offers a convenient method of power distribution and surge suppression in workbench, wall-mount or floor-mount applications. Includes six NEMA 5-15R outlets, six-foot (1.8-meter) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built-in surge suppression rated at 900 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige housing with black output receptacles and power cord.

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1449 3rd Edition (USA/400V rating), UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity
- 6-ft. (1.83 m) AC line cord
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

| OVERVIEW             |                                                                                         |
|----------------------|-----------------------------------------------------------------------------------------|
| UPC Code             | 037332101013                                                                            |
| Product Type         | Surge Protector                                                                         |
| Charging Form Factor | Strip                                                                                   |
| Device Compatibility | Chromebook; Computer; Laptop; Monitor/HDTV; Phone; Projector; Tablet; Video Game System |



Powering Business Worldwide

TRIPP LITE  
SERIES

| INPUT                              |                                                                                                    |
|------------------------------------|----------------------------------------------------------------------------------------------------|
| Nominal Input Voltage(s) Supported | 120V AC                                                                                            |
| Recommended Electrical Service     | 120V (110-125V)                                                                                    |
| Input Cord Gauge Type              | 14 gauge; SJT                                                                                      |
| Input Cord Gauge (AWG)             | 14                                                                                                 |
| Voltage Compatibility (VAC)        | 120                                                                                                |
| Maximum Surge Amps                 | 45000                                                                                              |
| Input Plug Type                    | NEMA 5-15P                                                                                         |
| Input Cord Details                 | SJT                                                                                                |
| Input Cord Length (ft.)            | 6                                                                                                  |
| Right-Angle Plug                   | No                                                                                                 |
| Input Cord Length (m)              | 1.83                                                                                               |
| Integrated Cord Clip               | No                                                                                                 |
| OUTPUT                             |                                                                                                    |
| Frequency Compatibility            | 50 / 60 Hz                                                                                         |
| Output (Watts)                     | 1800                                                                                               |
| Output Receptacles                 | (6) 5-15R                                                                                          |
| Circuit Breaker (amps)             | 15                                                                                                 |
| Transformer Accommodation          | (2) Yes                                                                                            |
| Outlet Orientation                 | Single row of outlets                                                                              |
| Right-Angle Outlets                | No                                                                                                 |
| USER INTERFACE, ALERTS & CONTROLS  |                                                                                                    |
| Diagnostic LED(s)                  | Yes                                                                                                |
| Switches                           | Combination AC circuit breaker and lighted two position power switch controls power to all outlets |
| Diagnostic LED Details             | Protection present (green)                                                                         |
| SURGE / NOISE SUPPRESSION          |                                                                                                    |
| AC Suppression Joule Rating        | 900                                                                                                |
| AC Suppression Response Time       | < 1 ns                                                                                             |
| Protection Modes                   | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression                       |
| UL1449 Let Through Rating          | 400V - UL Verified                                                                                 |
| EMI / RFI Filtering                | Up to 20 dB                                                                                        |
| Immunity                           | Conforms to IEE 587 / ANSI C62.41                                                                  |
| Automatic Shut-Off                 | Yes                                                                                                |



Powering Business Worldwide

TRIPP LITE  
SERIES

| DATALINE SURGE SUPPRESSION                                 |                                                                                                                          |
|------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------|
| Cable (Coax) Protection                                    | No                                                                                                                       |
| Network (Ethernet) Protection                              | No                                                                                                                       |
| Telephone/DSL Protection                                   | No                                                                                                                       |
| PHYSICAL                                                   |                                                                                                                          |
| Color                                                      | Beige                                                                                                                    |
| Material of Construction                                   | Metal                                                                                                                    |
| Wire Gauge (AWG)                                           | 14 AWG                                                                                                                   |
| Power Cord Color                                           | Black                                                                                                                    |
| Housing Color                                              | Beige                                                                                                                    |
| Mounting Holes or Slots                                    | Yes                                                                                                                      |
| Slot or Hole Mount Measurement (Center to Center)          | 165 mm                                                                                                                   |
| Outlets Measurement (Center to Center)                     | 38.89mm                                                                                                                  |
| Receptacle Color                                           | Black                                                                                                                    |
| Shipping Dimensions (hwd / in.)                            | 2.25 x 15.00 x 6.00                                                                                                      |
| Shipping Dimensions (hwd / cm)                             | 5.72 x 38.10 x 15.24                                                                                                     |
| Shipping Weight (lbs.)                                     | 1.77                                                                                                                     |
| Shipping Weight (kg)                                       | 0.80                                                                                                                     |
| Unit Dimensions (hwd / in.)                                | 1.500 x 12.750 x 2.500                                                                                                   |
| Unit Dimensions (hwd / cm)                                 | 31.75 x 6.35 x 3.8                                                                                                       |
| Unit Weight (lbs.)                                         | 1.25                                                                                                                     |
| Unit Weight (kg)                                           | 0.57                                                                                                                     |
| FEATURES & SPECIFICATIONS                                  |                                                                                                                          |
| Rotatable Outlets                                          | No                                                                                                                       |
| Antimicrobial                                              | No                                                                                                                       |
| STANDARDS & COMPLIANCE                                     |                                                                                                                          |
| Product Certifications                                     | cUL Listed; UL 1449; UL 1363; UL Listed                                                                                  |
| Product Compliance                                         | RoHS                                                                                                                     |
| WARRANTY & SUPPORT                                         |                                                                                                                          |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty                                                                                                |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$100,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a> |



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.