



PRODUCTS

Chilisin provides inductor turnkey solutions for EMI, power and RF and a global technical team to support its customers. Chilisin has become one of the few inductor suppliers capable of providing a complete "one-stop shopping" experience.



- Power Inductor
- Chip Inductor
- Bead
- Common Mode Choke

Product Search

Submit

CUW21

Home > Products > Common Mode Choke > CUW21

Part Number : CUW21T-900M-N

Size Code(JIS/EIA)	2012/0805
Impedance(?)	90
Tolerance(±%)	20
Test Frequency(MHz)	100
RDC(?)Max	0.35
IDC(mA)	330
Insulation Resistance (M?)	10
Rated Voltage(Vdc)	120
Operating Temperature	− 4 0 °C~ 1 0 5 °C(Including self - temperature rise)
L(mm)	2.05±0.20
W(mm)	1.25±0.20
T(mm)	1.2±0.20

- 1.RDC: SINGLE WIRE TEST VALUE
- 2.IDC for Inductance drop 10% from its value without current.

P/N	CUW21T-900M-N
Part Numbering	
Dimensions	
Packing	
Recommended Pattern	
Electrical Characteristics Curve	

P/N	CUW21T-900M-N400
Part Numbering	
Dimensions	
Packing	
Recommended Pattern	
Electrical Characteristics Curve	

Back

