



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Single Row Terminal Block

A38220907

UPC:051712294218

### Dimensions:

- **Height:** .001 IN
- **Length:** 4.36 IN
- **Width:** .65 IN

**Weight:**.1 LB

### Warranties:

- Not Applicable

### Specifications:

- **Application:** industrial
- **Mounting:** Flat base, barrier end
- **Special Features:** Break down voltage 3500V
- **Type:** Standard barrier
- **Voltage Rating:** 600V
- **Number Of Poles:** Nine-pole
- **Operating Temperature:** -40° to 105°C
- **Wire Size:** #22-12 AWG Cu
- **Torque Rating:** 9 lb-in
- **Center Spacing:** 0.437 in
- **Screw Options:** Steel SEMS zinc-plated screw
- **Material:** Molded thermoplastic base, zinc plated steel screw
- **Color:** Black
- **Connection:** #6-32 TPI screw, hand wired
- **Terminal Material:** Printed circuit

### Supporting documents:

- [Product Catalog](#)

**Certifications:** No Data

### Product compliance:

- CE Marked



