Part Number : 2037029400
Product Description : FineAdjust Applicator for Loxon Terminals, 12-10 AWG, UL 1015 Wire
Series Number : 207127
Status : Active
Product Category : Applicators and Crimp Modules



Documents and Resources

Tooling Specifications

2037029400-000.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

Downloaded from Arrow.com.

General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	FineAdjust Applicator for Loxon Terminals, 12-10 AWG, UL 1015 Wire
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	FineAdjust,Loxon
Tool Type	Applicator
UPC	196823539992
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
Loxon Locking Quick Disconnect,	194390005

Downloaded from Arrow.com.

Female, for 10-12 Wire, Reel, Tab 6.35 x 0.81mm	

Downloaded from Arrow.com.