




30 POSITION



60 POSITION



120 POSITION



240 POSITION

NOTES: UNLESS OTHERWISE SPECIFIED;

- 1 CONNECTOR MATERIALS:
HOUSING: GLASS FILLED THERMOPLASTIC,
UL94-V0 COMPLIANT.
TERMINAL: PHOSPHOR BRONZE ALLOY
- 2 PACKED IN TUBES.
- ③ FEATURE MAY OR MAY NOT BE PRESENT DEPENDING UPON THE MOLD TOOLING USED TO PRODUCE PRODUCT.
- 4 PRODUCT SPECIFICATION: GS-12-177.
- 5 APPLICATION SPECIFICATION: GS-20-015.
- 6 THE PRODUCTS WHERE THE PART NUMBER ENDS IN "LF" MEET THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 7 ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRARED OR VAPOR PHASE REFLOW OVEN.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	.X ±.3[±.1]	projection	title	www.fciconnect.com	
F	V04-1124	TAB	02/07/05		.XX ±.13[±.02]		T SERIES STRAIGHT RECEPT ASSY 5 ROW, STB		
G	V05-0438	VS	07/14/05		.XXX ±.051[±.005]				
H	DG08-0173	TER	7/22/08	angles	0° ±1°				
				dr	V.SEABASTIAN 07/14/05	MM	product family	METRAL	code
				enr	J.VOLSTROF 07/14/05		size	dwg no	213
				chr	J.VOLSTROF 07/14/05	scale			sheet
				appd	J.VOLSTROF 07/14/05	4:1			1 of 2
sheet index	revision sheet	H	H						
		1	2						

cage code
22526

