




Specifications:

Current Rating:1.5A AC/DC
Voltage Rating:230V AC/DC
Contact Resistance:20m ohm. Max.
Insulation Resistance:1,000M ohm. Min.
Withstanding Voltage:500V AC For One Minute
Operating Temperature Range:-40°C ~ +105°C
Material and Finish
Insulator:High Temp. Plastic (UL94V-0)
Contact:Phosphor Bronze
Plated:Tin Plated

How to Order

TMM-X-X-XX-X

- | | |
|-----------------------|--|
| Type | Packaging |
| 1-IDC Male | 1 - Tape & Reel with vacuum cap |
| 2-IDC Plug | 2 - Tube |
| 3-DIP Male Straight | 3 - Bag |
| 4-DIP Female Straight | 4 - Tape & Reel without vacuum cap |
| 5-DIP Female R/A | Number of Positions |
| 6-SMT Female Straight | 04, 06, 08, 10, 12, 14, 16, 18, 20, 22, 24 or 26 |
| Locking System | |
| 0-without lock | |
| L-with lock | |



Pos	A	B	C	Pos	A	B	C
4	9.70	3.81	5.60	16	24.94	19.05	20.84
6	12.24	6.35	8.14	18	27.48	21.59	23.38
8	14.78	8.89	10.68	20	30.02	24.13	25.92
10	17.32	11.43	13.22	22	32.56	26.67	28.46
12	19.86	13.97	15.76	24	35.10	29.21	31.00
14	22.40	16.51	18.30	26	37.64	31.75	33.54

PCB Layout



TOLERANCE (mm)	APPROVALS	DATE	TITLE	AMPHENOL
X. ±0.3	DRAWN Stephane	2009/10/07	TMM Series	Amphenol European Design Center
X.X ±0.2	CHECKED Rob	2009/10/07	SMT Female w/Lock	Scale N.A. Sheet 1 of 1
X.XX ±0.15	APPROVED Rob	2009/10/07		
UNLESS OTHERWISE SPECIFIED	UNIT: mm	SIZE: A4	DRAWING N° TMM-6-L-XX-X	REV. D