

1		2		3		4		5		6		7		8	
A															
B															
C															
D															
E															
F															
27		33612211000001		Fiber optic, single mode 9/125 μm				100							
26		33612210900001						90							
25		33612210800001						80							
24		33612210700001						70							
23		33612210600001						60							
22		33612210500001						50							
21		33612210450001						45							
20		33612210400001						40							
19		33612210350001						35							
18		33612210300001						30							
17		33612210250001						25							
16		33612210200001						20							
15		33612210150001						15							
14		33612210140001						14							
13		33612210130001						13							
12		33612210120001						12							
11		33612210110001						11							
10		33612210100001						10							
9		33612210090001						9							
8		33612210080001						8							
7		33612210070001		7											
6		33612210060001		6											
5		33612210050001		5											
4		33612210040001		4											
3		33612210030001		3											
2		33612210020001		2											
1		33612210010001		1											
Cont. no.		Part no.		Type of cable				Dim. a[m]							