





REVISIONS




P	LTR	DESCRIPTION	DATE	DWN	APVD
	K	REVISED TO MATCH THE PART REVISION	06NOV2019	MK	CF
	K1	REVISION RECORD UPDATED	12NOV2019	MK	CF
	K2	REVISED PER PCN-22-153957	18AUG2022	SN	AW
	K3	REVISED PER PCN-23-165384	19JAN2023	MK	AW



3-D VIEW
CLOSED




3-D VIEW
OPEN



4 CIRCULAR DIMENSIONS CAN NOT BE MEASURED WITHOUT USING A GAGE OR AN ADEQUATE CONNECTOR DUE TO WARPAGE AFTER DEMOLDING.

- 3. MATERIAL: NYLON 66, COLOR: BLACK
- 2. SUITABLE WITH CORRUGATED TUBES SIZE NW 17, 19 AND 26.
- 1. THIS PART MATES WITH HDP24/26-24-XP/SX-L017.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. MESSENGER 20OCT2004		 TE Connectivity							
DIMENSIONS: INCH[mm]		CHK A. JAIME 30SEP2008									
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. REED 01OCT2008		NAME COVER STRAIGHT SIZE 24 HDP L017 MODS ONLY TUBE SIZE NW 17, 19, 23 AND 26 						
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025[0.63] 4 PLC ± ANGLES ±0° 30' 0"		PRODUCT SPEC 108-151015								
			APPLICATION SPEC 114-151015								
	MATERIAL VYDYNE 47H PA 6/6		WEIGHT 30 g					SIZE A3	CAGE CODE 4AFU8	DRAWING NO C-2428-010-2405	RESTRICTED TO -
	FINISH - -		CUSTOMER DRAWING					SCALE 1:1	SHEET 1 OF 1	REV K3	