



Part Number : [1301540049](#)
Product Description : Watertite Extreme Inline GFCI
Molded Y Cordset, 2 Pole/3 Wire, Cordset Length
0.91m (3.0'), NEMA 5-15, 125V
Series Number : 130154
Status : Active
Product Category : Wiring Devices
Engineering Number : 14W47-Y-IN



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130154
Description	Watertite Extreme Inline GFCI Molded Y Cordset, 2 Pole/3 Wire, Cordset Length 0.91m (3.0'), NEMA 5-15, 125V
IP Rating	IP67
NEMA Configuration	NEMA 5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Molded Y Cordset
UPC	78678835612

Electrical

Current - Maximum per Contact	15.0A
GFCI	Yes-In-line
Voltage - Maximum	125V

Physical

Cord Grip Body Size	F2 1/2"
Cord Type	12/3 SJOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Lighted Connector	No
Locking Blade	No
Poles	2-pole/3-wire
Receptacle Type	Duplex