
Part Number : 1300080075
Product Description : Mini-Change B-Size Single-Ended Cordset, 10 Poles, Female (Straight) to Pigtail, 22 AWG, PVC Cable,10.0m (32.81') Length
Series Number : 130008
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 301000A04M100



Documents and Resources

Drawings

1300080075_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130008
Description	Mini-Change B-Size Single-Ended Cordset, 10 Poles, Female (Straight) to Pigtail, 22 AWG, PVC Cable,10.0m (32.81') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Single Ended
UPC	78678844523

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	600V

Physical

Cable Diameter	6.10mm (.240")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Push to Lock
Gender	Female-Pigtail
Keyway	Single

Downloaded from Arrow.com.

LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Brass
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	1180.990/g
Orientation	Straight to Pigtail
Poles	10
Temperature Range - Operating	-20° to +75°C
Wire/Cable Type	STOOW
Wire Size (AWG)	22

Downloaded from Arrow.com.