

**Part Number :** [901430004](#)

**Product Description :** 2.54mm Pitch C-Grid III  
Modular Crimp Housing, Dual Row, 4 Circuits, Black

**Series Number :** 90143

**Status :** Active

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[901430004\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-99020-0001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Contains Triphenyl-phosphate per D(2025)7771-DC (04 Feb 2026)   |
| EU RoHS            | Compliant per EU 2015/863   |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|              |  |
|--------------|--|
| Status       | Active   |
| Category     | Connector Housings   |
| Series       | 90143  |
| Description  | 2.54mm Pitch C-Grid III Modular Crimp Housing, Dual Row, 4 Circuits, Black |
| Application  | Signal, Wire-to-Board  |
| Comments     | No Buttons   |
| Product Name | C-Grid III   |
| UPC          | 800753655461   |

### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

### Physical

|                       |                    |
|-----------------------|--------------------|
| Circuits Detail       | No Voided Circuits |
| Circuits (maximum)    | 4                  |
| Color - Resin         | Black              |
| Gender                | Receptacle         |
| Glow-Wire Capable     | No                 |
| Keying to Mating Part | No                 |
| Lock to Mating Part   | No                 |
| Material - Resin      | PPO                |

|                               |                |
|-------------------------------|----------------|
| Net Weight                    | 0.224/g        |
| Number of Rows                | 2              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 2.54mm         |
| Pitch - Termination Interface | 2.54mm         |
| Polarized to Mating Part      | No             |
| Ports                         | 1              |
| Stackable                     | Yes            |
| Temperature Range - Operating | -55° to +105°C |

---

## Mates With / Use With

### Mates with Part(s)

| Description                             | Part Number  |
|---|--------------|
| C-Grid III Right-Angle Dual Row Headers | <u>90122</u> |
| C-Grid III Dual Row Headers             | <u>90130</u> |
| C-Grid III Vertical Dual Row Headers    | <u>90131</u> |

### Use with Part(s)

| Description   | Part Number      |
|---|------------------|
| Pre-Crimped Lead C-Grid III Female-to-C-Grid III Female, Tin (Sn) Plating, 150.00mm Length, 22 AWG, Black | <u>797582022</u> |
| Pre-Crimped Lead C-Grid III Female-to-C-Grid III Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black | <u>797582023</u> |
| C-Grid III Female Crimp Terminals   | <u>90119</u>     |

---

This document was generated on Apr 29, 2026