NEUTRIK



NC3MAAH

3 pole male XLR receptacle, grounding: separate ground contact to mating connector shell and front panel, horizontal PCB mount

Most cost-effective round plastic body XLR PCB mount panel connector. Front panel cutout and PCB layout 100% compatible to A series. "Tulip" type contact design with high contact pressure for highest durability. Flammability rating UL94HB. UL recognized component.

Features & Benefits

- Most cost-effective series
- "Tulip" type contact design with high contact pressure for highest durability
- Selective gold plated contact and PCB termination area for best conductivity and solderability

Technical Information

Product	
Title	NC3MAAH
Connection Type	XLR
Gender	male

All rights reserved / 10.05.2026

Downloaded from Arrow.com.

NEUTRIK

Electrical	
Capacitance between contacts	≤ 4 pF
Contact resistance	≤ 6 mΩ
Dielectric strength	1,5 kVdc
Insulation resistance	> 10 GΩ (initial)
Rated current per contact	6 A
Rated voltage	< 50 V
Grounding Options	Separate ground contact connected to mating connector shell and front panel, no connection to Pin 1

Mechanical	
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wiresize	
Wiring	Horizontal PCB mount
Locking device	Latch lock
Mounting direction	Rear mounting
Chassis shape	A
Mounting	A-Screw

Material	
Contacts	Brass (CuZn35Pb2)
Shell	Polyamide (PA 6.6 30 % GR)

All rights reserved / 10.05.2026

Downloaded from Arrow.com.

Environmental	
Approvals	UL
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

All rights reserved / 10.05.2026

Downloaded from Arrow.com.