

THIS DRAWING IS UNPUBLISHED.





RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		A1	REVISED PER ECR-06-023430	12OCT06	HMR GJ

- 1 SPECIFICATION: MAGNET WIRE #18-#34 AWG, .040-.006 [1.02-0.16 mm] DIA COPPER.
- 2 POCKET RECOMMENDATION: 1601424.
- 3 TERMINALS SUPPLIED ON REELS, CAN BE SUPPLIED LOOSE PIECE.
- 4

TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS SPECIFICATION 114-13166 FIGURE 5.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.S. FEHER 23SEP2005		POST TIN PLATE OVER NICKEL PLATE		1601214-2	
DIMENSIONS: INCHES		CHK G. JACONO 23SEP2005		FINISH		PART NUMBER	
		APVD G. JACONO 23SEP2005		NAME		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		PRODUCT SPEC 108-2085		STANDARD RANGE WIRE TO P.C.B. TAB SIAMEZE TERMINAL			
MATERIAL BRASS, H04		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01[0.25] 3 PLC ± .005[.13] 4 PLC ± - ANGLES ± 2° FINISH SEE TABLE		APPLICATION SPEC 4		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		WEIGHT -		A2 00779 C=1601214		SCALE 1:3 SHEET 1 of 1 REV A1	
		CUSTOMER DRAWING					