NUMBER C 153227.

3rd ANGLE (AMERICAN) PROJECTION

DIMENSIONS IN INCHES. DO NOT SCALE PRINT
DIMENSIONS THUS [ ] IN MM.

.156[3.96]DIA. MIN.

.118[2.997]
.115[2.921]
DIA.

SECTION AA

.180[4.57]
.155[3.94]

SECTION BB


.235[5.97]
.210[5.33]

SECTION CC

INSULATION .120-.170[3.05-4.32]

.050[2.03]

.140[3.56]



NOTE:
PUSH-ON AND PUSH-OFF FORCES WITH THE RESPECTIVE COUNTERPART TO BE WITHIN 5-12N.

PART No	FINISH	MATERIAL
~~1-153227-1~~	~~PRE-TIN~~	~~BRASS(REVERSE REELING)~~
153227-6	SILVER	BRASS(FOREIGN PROD.ONLY)
~~153227-5~~	~~PRE-TIN~~	~~PHOS. BRONZE~~
153227-4	ELEC.-TIN	BRASS
153227-3	NONE	PHOS. BRONZE
~~153227-2~~	~~NONE~~	~~BRASS~~
~~153227-1~~	~~PRE-TIN~~	~~BRASS~~

© AMP of GREAT BRITAIN LTD 1971.

CUSTOMER COPY
REFERENCE ONLY

LTR	REVISION RECORD	DR	CHK	DATE
P1	ECN-25-360107	WLS	JP	18DEC25

PRINT DIST

DR P SMITH 5.11.71
CHK P.J. MAGUIRE 7/11/71

MATERIAL AND FINISH
.013[0.33]
TOCK
& SEE TABLE

WIRE — RANGE — INSULATION
2.0-3.5mm2(see above)

TOLERANCE EXCEPT AS NOTED
± .015 [0.38] ± 1° 0'

SCALE 4:1

AMP of Great Britain Ltd
TERMINAL HOUSE, STANMORE, MIDDX.

CLASS

TYPE

LOC E A NO C-153227 REV P1

NAME -118 [3] LANCED SOCKET.

BAF 8265/70

Downloaded from Arrow.com.