Part Number : 731570260
Product Description : Precision Test Connector, 1.85mm PCB Jack Receptacle, 2-Hole Flange Mount, Solderless Compression Contact, Stripline, without Screws, 50 Ohms
Series Number : 73157
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

731570260_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

896755260-000.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73157
Description	Precision Test Connector, 1.85mm PCB Jack Receptacle, 2-Hole Flange Mount, Solderless Compression Contact, Stripline, without Screws, 50 Ohms
Application	RF
Product Name	Precision Test - 1.85mm
Style	PCB
Type	Subminiature
UPC	198930253228

Electrical

Frequency	67 GHz
Impedance	50Ω

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Orientation	Straight
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount - Compression
Reverse Polar	No
Wire/Cable Type	N/A

Downloaded from Arrow.com.

Downloaded from Arrow.com.