

# Catalog

Home &gt; Catalog



Home &gt; 7464-B-440-AL



## Full Knurled Swage Standoffs

Model: 7464-B-440-AL

## Select Finish

 -0 No Plate 

## Select Finish

 -0 No Plate 

 Choose a CAD format 


### Product Details

These standoffs are made of Aluminum. They are Round shaped with diameter as 1/4". The thread for this part is 4-40 and length is 11/16".

#### SWAGE TOOLING

±.003	S	P
.075	A	1/32
.105	B	1/16
.135	C	3/32
.165	D	1/8
.230	E	3/16
.290	F	1/4

#### PDF Catalog

[RAF\\_catalog\\_0151.pdf](#)

Thread	4-40
O.D.	1/4"
Shape	Round
Length (L)	11/16"
Material	Aluminum
RoHS	Yes
Shank Length	0.105"
Board Thickness	1/16"
Shank Diameter	0.201"
Thread Clearance	0.150"
Finish	-0 No Plate



#### Technical Information


[Electronic Hardware Components](#)
[Engineering Data](#)
[Capabilities Brochure](#)
[Services](#)
[Distributors](#)

#### Company

[RAF Quality Management](#)
[Industry Links](#)
[What's New](#)
[News](#)
[About](#)
[Contact](#)
[Careers](#)

#### Contact Us

#### Find Us


 95 Silvermine Rd.  
Seymour CT 06483

 Downloaded from [Arrow.com](#).