




**Part Number :** 152670335

**Product Description :** 1.00mm Pitch Premo-Flex FFC  
Jumper, Same Side Contacts (Type A), 51.00mm Cable  
Length, Tin (Sn) Plating, 18 Circuits



**Series Number :** 15267

**Status :** Active

**Product Category :** Flat-Flexible Cable (FFC)

## Documents & Resources

### Drawings

152670335\_sd.pdf

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-15267-001-001.pdf

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15267
Description	1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 51.00mm Cable Length, Tin (Sn) Plating, 18 Circuits
Comments	Contacts on the same side, Type A
Product Name	Premo-Flex FFC Jumper
UPC	884982443471

### Agency

UL	E29179
----	--------

### Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	60V AC

### Physical

Cable Length	51.00mm
Circuits (Loaded)	18
Contact Layout Type	A (same side)
Design Feature	Flexible
Flammability	94V-0

Material - Plating Mating	Tin
Net Weight	0.720/g
Packaging Type	Bag
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-40° to +105°C
Termination Style	FFC Connector
Wire/Cable Type	Flat Flex Cable
Wire Size (AWG)	N/A

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Bottom Contact, 3.00mm Height, 18 Circuits, Tin-Bismuth Plating	<a href="#"><u>522711879</u></a>
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Vertical, 5.75mm Height, 18 Circuits, Tin-Bismuth Plating	<a href="#"><u>526101871</u></a>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, 18 Circuits	<a href="#"><u>528081870</u></a>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, with Pick-and-Place Polyimide Tape, 18 Circuits	<a href="#"><u>528081871</u></a>
Easy-On FFC/FPC Connector, 1.00mm Pitch, Slider Series, Right-Angle, Top Contact, 2.70mm Height, 18 Circuits, Tin-Bismuth Plating	<a href="#"><u>522071885</u></a>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Right-Angle, Non-ZIF, Top Contact Style, 18 Circuits	<a href="#"><u>527931870</u></a>
1.00mm Pitch Easy-On FFC/FPC	

Connector, Vertical, Surface Mount Compatible, Non-ZIF, Kinked PC Tails, 18 Circuits	<u>528061810</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Non-ZIF, Top Contact Style Receptacle, 18 Circuits	<u>528071810</u>
1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Right-Angle, Non-ZIF, Bottom Contact Style, 18 Circuits	<u>528521870</u>

---

This document was generated on Sep 22, 2025