



Part Number : [2290961225](#)

Product Description : Pre-Crimped Lead Zero-Hachi Female-to-Zero-Hachi Female, 0.10µm Gold (Au) Plating, 500.00mm Length, 28 AWG, Black

Series Number : 229096

Status : Active

Product Category : Power and Signal Cable Assemblies




Documents and Resources

Drawings

[2290961225 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	229096
Description	Pre-Crimped Lead Zero-Hachi Female-to-Zero-Hachi Female, 0.10µm Gold (Au) Plating, 500.00mm Length, 28 AWG, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Zero-Hachi Terminal-to-Zero-Hachi Terminal
Keyword	Pre-Crimped Leads
Product Name	Zero-Hachi
UPC	198930256212

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Cable Length	500.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.625/g

Packaging Type	Bag
Plating min - Mating	0.100µm
Plating min - Termination	0.050µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10064
Wire Size (AWG)	28

Mates With / Use With

Use with Part(s)

Description	Part Number
Zero-Hachi Single Row Receptacle Housings	<u>214719</u>

This document was generated on Feb 01, 2026