

[Labels](#) / [Circuit Board Labels](#) / [Not for Wash Polyester Labels](#) /

3" Core Series ToughBond Glossy Polyester Labels



3" Core Series ToughBond Glossy Polyester Labels

Part Number:

THT-149-422-10

Label/Tape Size:

0.5 in H x 0.5 in W

Material:

Polyester

Material Number:

B-422

Color:

White

For Use with Printer:

BBP®81 Label Printer, BRADY IP® Series
Label Printer, BradyPrinter i7100,
BRADYPRINTER PR Plus Series Label Printer

ADD TO CART

1

PEOPLE ALSO VIEWED

OVERVIEW

Thermal transfer printable, glossy Permanent Polyester (B-422) labels are ideal for use in all commercial and industrial applications.

- Aggressive adhesive good for powder-coated and textured flat surfaces including low surface energy plastics
- Designed to withstand exposure to numerous solvents
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC; UL approved; CSA accepted
- Service temperature of -40 to 212° F (-40 to 100° C)

SPECIFICATIONS

Anti-Skid Surface?	N/A
Material Number	B-422
Dimensions	0.5 in H x 0.5 in W
UOM	Roll of 10000 Labels
Finish	Gloss
Indoor or Outdoor Use	Outdoor Use
Label/Tape Size	0.5 in H x 0.5 in W
Maximum Service Temperature °F	212 °F
Minimum Service Temperature °F	-40 °F
Printable Area Dimensions	0.5 in H x 0.5 in W
Printable Area Height	0.5 in
Printable Area Width	0.5 in
Product Number	62284
UPC	662820622840

Quantity per Roll	10000
Quantity per Row	4
Secondary Label Included	Secondary Label is Not Included
Tamper Indication Type	N/A
Thickness	0.004 in
Trade Name	ToughBond®
Adhesive Type	Acrylic
Applications	Asset Tracking, Barcode Labeling, Circuit Board ID - Through Hole Top, Component & Equipment ID, General & Industrial ID, Outlet Faceplates, Panel Labeling, Rating Plates
Color	White
For Use with Printer	BBP®81 Label Printer, BRADY IP® Series Label Printer, BradyPrinter i7100, BRADYPRINTER PR Plus Series Label Printer
Label/Media Format	Roll
Material	Polyester
Material Properties	N/A
Print Technology	Thermal Transfer
Resistance Properties	Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
Shape	Square
Suggested Ribbon Series	R4400, R4900, R6000, R6200

Solutions

[Floor Marking Guide](#)
[GHS Label Compliance](#)
[Lockout Tagout Compliance](#)
[Arc Flash Labeling Requirements](#)
[Cable and Wire Label Options](#)
[Product and Barcode Labeling](#)
[Brand Protection Solutions](#)

Services

[Lockout Tagout Services](#)
[Arc Flash Services](#)
[Confined Space Services](#)
[Visual Workplace Services](#)
[Hazcom GHS Services](#)
[Software Programming & Integration](#)
[Label Template & File Conversion](#)
[Printer Use & Training](#)
[Printer Preventative Maintenance](#)
[Toll and Custom Coating](#)
[Authentication & Tracking Services](#)

Help

[Contact Us](#)
[Knowledge Center](#)
[Printer Drivers & Firmware](#)
[Brady Software Updates](#)
[Safety Data Sheets](#)
[Technical Data Sheets](#)
[WEEE-RoHS Compliance](#)
[Product Certification](#)
[Printer Registration](#)

Resources

[Find a Distributor](#)
[Printer Selection Tool](#)
[Label Selection Tool](#)
[Digital Catalog](#)
[Request a Catalog](#)



Brady
(NYSE:BRC)
is a
manufacturer
of complete
solutions
that
identify and
protect
people,
products
and places.
Brady's
products
help
customers
increase
safety,
security,
productivity
and
performance
and include
high-
performance
labels,
signs, safety
devices,
printing
systems
and
software.

Contact
6555
W.
Good
Hope
Rd.
Milwaukee
WI
53223
Phone:
888-
250-
3082
Hours:
7am-
6pm
CST
Monday
-
Friday

About
Corporation
Privacy
Policy
Terms
and
Conditions
Terms
of Use
ISO
Certificates

Other
Brady
Sites
Distributor
Portal
International
Sites
Safety
Services
&
Software
Smart
ID
Brand
Protection



© 2018 Brady Worldwide, Inc.