



Part Number : 1301350323  
Product Description : Super-Safeway 500W  
Halogen Floodlight Stand Mount, 16/3 SOOW  
Cord Type, Overall Cord Length 7.62m (25.0')  
Series Number : 130110  
Status : Active  
Product Category : Lamps and Lights  
Engineering Number : 8506



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130110
Description	Super-Safeway 500W Halogen Floodlight Stand Mount, 16/3 SOOW Cord Type, Overall Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678800030

## Electrical

Lamp Wattage - Maximum	500W
Lumens	9200
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

## Physical

Bulb Type	Quartz Halogen
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	N/A
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	374.65mm (14.750")
Lamp Type	T-3 RSC
Length	279.40mm (11.000")
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Stand
Outlet	None
Packaging Type	Carton

---

This document was generated on Apr 22, 2025