

Downloaded from Arrow.com.


Copyright FCI.


FCIconnect.com

PRODUCT NUMBER	PITCH
KTxx01x000J0G	7.62 mm









SECTION P-P

Material:

- Item ⓐ Terminal(housing) :Thermoplastic (UL94V-0)
- Item ⓑ Terminal(cover) : Thermoplastic (UL94V-0)
- Item ⓒ Terminal screw : Steel Zinc plating " - " slot type
- Item ⓓ Clamp : Brass, Ni plated
- Item ⓔ Female contact : Copper.Tin plated

Electrical cULus

- Voltage rating: 600VAC (match with ET sereis);300VAC(match with KS series)
- Current rating: 41A
- Solid wire (AWG): 8-24
- Stranded wire(AWG): 8-24
- Torque: 9.0 Lb-In
- Screw: M3.5
- Wire strip length: 10-11mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:

N=Number of poles

Dim A	N×7.62
Dim B	(N-1)×7.62

Dimension

Poles	Tolerance
2P-5P	±0.20
6P-10P	±0.30
11P-16P	±0.40

PART NO.: KT xx 01 x 0 00J0 G

		Color		RoHS compliant
Solid block	0	Black (RAL9005)		(lead<4%)
No. of poles	2	Red (RAL3001/D)		In copper Alloy
02 2 poles	3	Orange(RAL2011/P)		
03 3 poles	4	Yellow(RAL1018/A)		
... ...	5	Green(RAL6018/T)		
16 16 poles	6	Blue (RAL5015/A)		
	8	Grey(RAL7035/D)		
	9	White(RAL1102)		
	C	Green(RAL6018/U)		

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family: TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title: TERMINAL BLOCK PLUGGABLE PLUG
				angles	linear X.±0.5 / X.X±0.3 / X.XX±0.1	MM	
				X°±1°		scale	
				dr	EVIN ZHONG 050614		dwg no: KTxx01x000J0G — sheet 1 of 1 — size A4
				engr	EVIN ZHONG 050614		
				chr	HANKE FENG 050614		type: CUSTOMER Drawing
				appd	SHI JUN 050614		
sheet index	revision	A					
	sheet	1					