



+ CONNECTORS
RF CONNECTORS



✓ Active

TE CONNECTIVITY (TE)
2064 5059 00
Subminiature Coax | SM , SMA

1053392-1
TE Internal Number: 1053392-1
Alias ID: 2064-5059-00

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Connector Interface SMA

Connector Style Jack

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]

Impedance (Ω) 50

Operating Frequency (GHz) 12.4

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

OSM POLARIZED PRINTED WIRING BOARD RIGHT ANGLE JACK RECEPTACLE
PDF (TIFF AVAILABLE)
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.
Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface SMA
Connector Style Jack
Connector & Contact Terminates To Printed Circuit Board

Configuration Features

PCB Mounting Orientation Right Angle

Electrical Characteristics

Impedance (Ω) 50

Body Features

Body Material Stainless Steel
Body Plating Material Gold

Contact Features

Center Contact Plating Material Gold over Nickel
Center Contact Material Beryllium Copper
Connector Product Type Connector Assembly
RF Connector Contact Configuration Captivated Contacts

Dimensions

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]
Length 14.81 mm [.583 in]

Operation/Application

Operating Frequency (GHz) 12.4

Packaging Features

Packaging Method Package

Other

Dielectric Material TFE Fluorocarbon

PRODUCT COMPLIANCE +

Statement of Compliance

Statement of Compliance
PDF