Part Number : 1301370014
Product Description : Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, F4 (1") Cord Grip Body, Box only, Yellow
Series Number : 130137
Status : Active
Product Category : Power Distribution
Engineering Part Number : 3091



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Power Distribution
Series	130137
Description	Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, F4 (1") Cord Grip Body, Box only, Yellow
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678830227

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	Per Cust. Supplied Receptacle
GFCI	Yes
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	Per Cust. Supplied Receptacle

Physical

Cord Diameter	19.05-24.64mm (.750-.970")
Cord Grip Body Size	F3 3/4"
Cord Length	N/A
Cord Type	N/A
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable

Downloaded from Arrow.com.

Number of Receptacles	2 - Customer Supplied
Packaging Type	Carton
Receptacle Type	N/A

This document was generated on Jan 04, 2026

Downloaded from Arrow.com.