

Representative Image

Catalog No. TY523MR

Description: CBL TIE 18LB 4IN NATURAL NYL

UPC No 5414363065371

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 92mm (3.6 Inches), Width of 2.3mm (0.09 Inches), Thickness of 1mm (0.04 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Euroslot Packaging

Descriptors

Category	Cable ties

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds , 80 newtons

Classifications

Brand Name	Ty-Rap

Dimensions

Width	0.09 in , 2.3 mm
Length	3.6 in , 92 mm
Thickness	0.04 in , 1 mm
Bundle Diameter	0.06 to 0.63 in , 1.5 to 16 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC000046 Cable tie
Band width	2.3 mm
Length belt/tape/tie	92 mm
Length belt/tape/tie	3.6 inch

by ABB

Downloaded from Arrow.com.

ETIM	EC000046 Cable tie
Tie thickness	1 mm
Tie thickness	0.043 inch
Max. bundle diameter	16 mm
Min. holding force	80 N
Operation temperature	-60-+85 °C
Operation temperature	-76-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	Y
UL approval	Y

Downloaded from Arrow.com.