



Part Number : [393570015](#)
Product Description : 3.50mm Pitch Beau Eurostyle
Fixed Mount PCB Terminal Block, 15 Circuits
Series Number : 39357
Status : Active
Product Category : Terminal Blocks and Barrier
Strip
Engineering Part Number : MX-MTB15008-0N



Documents and Resources

Drawings

[393570015 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39357
Description	3.50mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, 15 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Eurostyle Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	756054634264

Agency

UL	E48521
----	--------

Electrical

Current - Maximum per Contact	17.5A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Black

Entry Angle	Horizontal
Flammability	94V-0
Lock to Mating Part	No
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	3.50mm
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	No
Shrouded	Shrouded
Stackable	Yes
Temperature Range - Operating	-30° to +85°C
Wire Size (AWG)	16, 18, 20, 22, 24, 26, 28
Wire Size mm ²	0.20-1.00

This document was generated on May 06, 2026