



Languages ▼

Registered users

Login

PasswordGO

[Forgot password?](#) [Register Now](#)

search: GO

- ▶ PRODUCTS
- ▶ CONNECTION TYPE
- ▶ PRODUCT MICROSITES
- ▶ APPLICATIONS

Home

- Quick Links
- Cross reference
- RoHS/LF P/N Search
- Industry Standards
- Alphabetical List
- Documentation
- 3D model search
- Customer drawing search
- Multi Selection Search
- Search by category

Start > Search=YK33227030J0G* > YK33227030J0G

YK33227030J0G

YK33227030J0G - Terminal Blocks : Barrier Terminal Block, 8.25mm pitch, 27 position



Customer drawing

Environmental Compliance Report

ACTIVE

Distributor Stock

Print Datasheet

FCI Brings You More

- Contact our sales/technical support
- Sample request

Specifications

Download document

General	Dimensional	Electrical	Physical	Approvals / Certifications	Mounting
General					
Packaging				Box	
Product Type				Barrier Terminal Block	
Series				YK332	
Number of Positions				27	
Dimensional					
Solid wire size (AWG)				22 to 12	
Stranded wire size (AWG)				22 to 12	
Pitch				8.25 mm	
Screw Size				M3.0	
Electrical					
Withstanding Voltage				AC 2500 V/Min	
Current rating				20 A	
Voltage rating				300 V	
Physical					
Soldering temperature (celcius)				260 +/- 5 Celcius (5 sec)	
Color (Housing)				Public	
Material (Housing)				Barrier Terminal Block 8.25mm	
Terminal material				Brass	
Terminal plating				Tin	
Screw material				Steel	
Screw plating				Zinc	
Connection Type				Screw connection	
Temperature (Operating - range)				-40 to 115 Celcius	
Torque				8.8 Lb-in	
Approvals / Certifications					
Approvals / Certifications				cULus, CQC	
Mounting					
Board attachment				TMT	