








Loading plan



- Protection level: IP 67
- Temperature range: -25°C...+80°C

- Electrical data:
- Rated voltage: 15-30V DC
 - Nominal: 2 A per Contact
 - Current: 6 A max total

PUR, max. 16x0.34 + 2x0.75	10
Type of cable	Dim. a[m]

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
HARTING	All rights reserved	Created by	Inspected by	Standardisation	Date	State	
	Department HCS - RO	MUNTEANV	POPESCU	AVRAM	2017-04-24	Final Release	
HARTING Customised Solutions		Title		Doc-Key / ECM-Nr.		Page	
D-32427 Minden		har-SAB M8/4/4p PAC		100689718/UGD/000/C		1/1	
		Type	Number	Rev.			
		TB	090700101100	C			