



Corr. Loom Tubing Nylon, 1.303" (33.1mm) x 50', HS Black,PK1

CLT125N-L630

The CLT125N-L630 Corrugated Loom Slit Wall Tubing protects cables from impact and abrasion. Features a slit for easy installation onto a bundle of wires or a pre-assembled harness assembly, increasing productivity. Hold in place with cable ties and accessories. Suitable for indoor applications. UL94-HB flammability rating and a maximum temperature rating of 230°F (110°C). Heat-Stabilized Nylon 6. Inside diameter 1.303" (33.10mm). Color HS Black. 1 per package.

Specifications

Product Type	Corrugated Loom Tubing
Color	Black
Environment	Indoor
Flammability Rating	UL94-HB
Inside Diameter (In.)	1.3
Inside Diameter (mm)	33.1
Material	Nylon 6
Resistance Properties	Abrasion-Resistant
Maximum Operating Temperature (°C)	110
Minimum Operating Temperature (°F)	-40
Maximum Operating Temperature (°F)	230
Minimum Operating Temperature (°C)	-40
Nominal Diameter (In.)	1.25
Nominal Diameter (mm)	31.75
Outer Diameter (In.)	1.524
Outer Diameter (mm)	38.71
Overall Length (ft.)	50
Overall Length (m)	15.2
Standards Met	RoHS Compliant
Part Features	Provides protection for cables, crush impact and abrasion resistant

Packaging Detail

UPC	07498353307
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	2.4780
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000