

General Information

Extended Product Type:	DR4/6.G
Product ID:	1SNA110434R1500
EAN:	3472591104349
Catalog Description:	DR4/6.G Specific Terminal Blocks Grey
Long Description:	DR4/6.G Specific Terminal Blocks Miniblocks.

Ordering

Color:	Grey
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0205_CHB4
Instructions and Manuals:	1SNC160001C0205_CHB4

Dimensions

Product Net Width:	6 mm
Product Net Height:	29 mm
Product Net Depth / Length:	28.5 mm
Product Net Weight:	5 g

Technical

Rated Cross-Section:	2.5 mm ²
Spacing:	6 mm
Connection Type:	Quick-connect - Screw clamp
Function:	Miniblock
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 ... 4 mm ² Screw Clamp / Rigid 1x 0.2 ... 4 mm ²
Rated Current (I_n):	Main Circuit 20 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 300 A
Rated Voltage (U_r):	380 V
Mounting on DIN Rail:	TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	9.5 mm

Recommended Screw Driver:	4 mm
Tightening Torque:	acc. IEC 60947-1 0.5 N·m Manufacturer 0.8 N·m

Technical UL/CSA

Connecting Capacity UL/CSA:	Stranded 12 AWG
Flammability According to UL94:	V2

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SND225004U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220003E1002
Instructions and Manuals:	1SNC160001C0205_CHB4
RoHS Information:	1SND230021F0201

Classifications

Object Classification Code:	X
ETIM 4:	EC000897 - Feed-through terminal block
ETIM 5:	EC000897 - Feed-through terminal block
ETIM 6:	EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	66 mm
Package Level 1 Depth / Length:	150 mm
Package Level 1 Height:	41 mm
Package Level 1 Gross Weight:	0.25 kg
Package Level 1 EAN:	3472591104349
Package Level 2 Units:	1750 piece
Package Level 3 Units:	84000 piece
Product Packing Type:	Box



