



Home > UES1102SM (#16636)

Products

- Product Directory
- Applications Directory
- Parametric Search

UES1102SM (#16636)

Overview

Diagrams

Description
2.5A, 100V Surface Mount Ultra-fast Rectifier

Shipping TR7

Electrical Rating	Symbol	Min	Typ	Max	Unit
Forward Voltage	V _F			0.98	V
Reverse Current	I _R			2.00	µA
Reverse Recovery Time	t _{rr}			25.00	ns

Maximum Electrical Rating	Symbol	Min	Typ	Max	Unit
Forward Current (Surge Peak)	I _{FSM}			35.00	A
Output Current	I _O			2.50	A
Working Peak Reverse Voltage	V _{RWM}			100.00	V

This part can be found in the following product categories:
Discretes > Rectifiers & Bridges > Ultra Fast Rectifier (trr less than 100ns)

Related Links

- Technical support
- Sales Contacts
- Available Stock
- Sales Contacts
- RFQ/Samples