



Part Number : [1301430104](#)

Product Description : Super-Safeway Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V

Series Number : 130143

Status : Active

Product Category : Wiring Devices


Engineering Part Number : 1447B163



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130143
Description	Super-Safeway Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V
IP Rating	N/A
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Specialty	N/A
Type	Cordset
UPC	78678879554

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	16/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')

Lighted Connector	No
Locking Blade	No
Net Weight	1.000/g
Poles	2-pole/3-wire
Receptacle Type	Single

This document was generated on May 27, 2026