



Part Number : [643341001](#)

Product Description : 2.50mm, 3.70mm CMC Header, Sealed, Right-Angle, 32 Circuits, 1 Port, Black

Series Number : 64334

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[643341001_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications


[643340000-AS-000.pdf](#)

[643340000-AS-CH-000.pdf](#)

[643340000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclhexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	64334
Description	2.50mm, 3.70mm CMC Header, Sealed, Right-Angle, 32 Circuits, 1 Port, Black
Application	Automotive, Power, Wire-to-Board
Comments	Coding: Black
Component Type	PCB Header
Product Name	CMC
UPC	191128880282

Electrical

Current - Maximum per Contact	12.0A, 2.5A
Voltage - Maximum	14V DC

Physical

Breakaway	No
Circuits (Loaded)	32
Circuits (maximum)	32
Color - Resin	Black
Durability (mating cycles max)	20
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	32.885/g
Number of Rows	4
Orientation	Right Angle
Packaging Type	Tray
Pitch - Mating Interface	2.50mm, 3.70mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Solder or Weld

Mates With / Use With

Mates with Part(s)

Description	Part Number
.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Left Wire Output, Black Coding, Mat Sealed	<u>643191211</u>
.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Right Wire Output, Black Coding, Mat Sealed	<u>643193211</u>

This document was generated on Apr 16, 2026