




REV.	DATE	ECR NO.	DESCRIPTION
A	11/21/11	2253	CHANGE THE DESIGN



1. IMPEDANCE: 50 OHM
2. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS. MIN.
3. DURABILITY: 500 CYCLES MIN.
4. TEMPERATURE RANGE: -65°C TO +165°C

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		APPROVALS		DATE		Amphenol Connex					
					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm		DRAWN M.ZHANG		11/21/11							
					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"		CHECKED									
4	CONTACT PIN	BERYLLIUM COPPER	GOLD	1			ISSUED				PART DESCRIPTION SMA JACK TO PLUG THRU BNC ADAPTER					
3	HOUSING	BRASS	NICKEL	1			SHEET 1 OF 1									
2	INSULATOR	PTFE	NATURAL	1							PART NO. 132375					
1	BODY	BRASS	NICKEL	1												
							CAD FILE		C:/CONNEX/132375.DWG		DWG. NO.		132375.DWG	REV. A	SIZE A	SCALE NA
					DO NOT SCALE DRAWING											