

- Quick Links
- Cross reference
- RoHS/LF P/N Search
- Industry Standards
- Alphabetical List
- Documentation
- 3D model search
- Customer drawing search
- Multi Selection Search
- Search by category

Start > Search=10132447-111PLF* > 10132447-111PLF

10132447-111PLF

10132447-111PLF - Minitek® Pwr 3.0 HCC : Minitek® Pwr 3.0 HCC Female Terminal, Gold Flash plating, AWG #16-#20, Pre-plated



Customer drawing

Product Environmental Compliance Report

ACTIVE



Distributor Stock

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Specifications

Download document

General Dimensional Electrical Mechanical Physical Approvals / Certifications Other Features

General	
Number of contacts	1
Series	10132447
Dimensional	
Pitch	3.0
Electrical	
Withstanding Voltage	1000_VAC
Current rating	Up_to_12.5_Amps
Resistance (Contact)	20_millichm_max_final 10_millichm_max_initial
Resistance (Insulation)	1000M_ΩMin_
Voltage rating	250V
Mechanical	
Durability (Mating cycles)	100_Cycles
Insertion force	8.0N_max
Withdrawal Force	3.7N_min
Physical	
Material (Contact)	High Conductivity Copper Alloy
Plating (Contact area)	Gold Flash
Temperature (Range)	-40°C_to_+105°C
Approvals / Certifications	
Approvals / Certifications	In Process
Other Features	
Packaging (Type)	Paper Reel

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.