



☐ World Wide [Change](#)
[Home](#)[Product Support](#)[Service Selector](#)[How to Buy](#)

S Type AV Power Conditioner with Battery

APC AV S Type Universal Rail Kit

SRAILKIT

[Email Technical Specification](#)
 [Printer Friendly](#)



Designed for all S Type models, the SRAILK four post racks with depths ranging from 20" All necessary mounting hardware is includec

IncludesInstallation guide, Mounting Hardwa Rack Mounting brackets, Screws

☐ [More Images](#)

Standard Lead TimeUsually in Stock

[Technical Specification](#) [Product Overview](#) [Compare Models](#)

Physical

Net Weight
1.59 KG
Maximum Height
51.00 mm
Maximum Width
533.00 mm
Maximum depth
89.00 mm
Shipping Weight
2.50 KG
Shipping Height
64.00 mm
Shipping Width
591.00 mm
Shipping Depth
108.00 mm
Color
Silver
Units per Pallet
105.00

Environmental

Operating Environment
0 - 70 °C
Operating Relative Humidity
0 - 95%
Operating Elevation
0-15000 meters
Storage Temperature
0 - 70 °C
Storage Relative Humidity
0 - 95%
Storage Elevation
0-15000 meters

Conformance

Standard Warranty
2 years repair or replace