



## NC3MDM3-H

3 pole male receptacle, horizontal PCB mount, Nickel housing, silver contacts, M3 mounting holes

Universal D-size metal body XLR panel mount series for pcb mount applications. Insert is removable from shell for ease assembling. UL recognized component.

## Features & Benefits

- ✓ D-shape metal shell
- ✓ Optimal RF protection using 3 shield contacts
- ✓ Insert is removable from rear of connector and locked into place by internal latch - permitting assembling and testing of pcb before assembling into housing
- ✓ Front or rear panel mount

## Technical Information

Product	
Title	NC3MDM3-H
Connection Type	XLR
Gender	male

## Electrical

Capacitance between contacts	$\leq 4 \text{ pF}$
Contact resistance	$\leq 5 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	6 A
Rated voltage	$< 50 \text{ V}$

## Mechanical

Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	$> 1000$ mating cycles
Wiresize	
Wiring	Horizontal PCB mount
Locking device	Latch lock
Mounting direction	Rear mounting
Chassis shape	D
Mounting	Mounting holes with M3 threads

Material	
Contact plating	2 µm Ag over 2 µm Ni
Contacts	Brass (CuZn35Pb2)
Insert	PA66
Locking element	Steel Ck67
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel

Environmental	
Approvals	UL
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C