Part Number : 2159131006
Product Description : Mini-Fit Max Receptacle Housing, Single Row, UL 94V-0, 6 Circuits, Glow-Wire Capable, Black
Series Number : 215913
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

2159131006_sd.pdf

2125140001-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2125150001-AS-000.pdf

2125150000-PS-000.pdf

2125150000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	215913
Description	Mini-Fit Max Receptacle Housing, Single Row, UL 94V-0, 6 Circuits, Glow-Wire Capable, Black
Application	Wire-to-Board, Wire-to-Wire
Component Type	Receptacle
Product Name	Mini-Fit Max
UPC	195842607958

Agency

UL	E29179

Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	No
Lock to Mating Part	Yes

Downloaded from Arrow.com.

Material - Resin	Nylon
Net Weight	1.707/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Max Vertical Single Row Headers	215915
Mini-Fit Max Right-Angle Single Row Through Hole Headers	220924
Mini-Fit Max Vertical Single Row Headers	224491
Mini-Fit Max Right-Angle Single Row Headers	224900

Use with Part(s)

Description	Part Number
Mini-Fit Max Female Crimp Terminals	212515
Mini-Fit Max Terminal Position Assurance (TPA) Retainers	212516

Downloaded from Arrow.com.