



[CONNECTORS](#)
[RF CONNECTORS](#)



✓ Active

TE CONNECTIVITY (TE)

SMA R/A PLG S/CLMP RG174 GSS

Subminiature Coax | SMA

1-1478912-0

TE Internal Number: 1-1478912-0

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

Connector Interface SMA

Connector Style Plug

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]

Cable Type KX 22A, KX 3B, RG 174A, RG 188A, RG 316, URM 95

Sealable No

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

SMA RIGHT ANGLE PLUG SOLDER, CLAMP RG188A/U, 316/U, RG174A/U, URM95, KX38, KX22A

PDF (TIFF AVAILABLE)

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

3D

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface SMA

Connector Style Plug

Sealable No

Connector & Contact Terminates To Wire & Cable

Body Features

Cable Connector Orientation Right Angle

Body Material Stainless Steel

Body Plating Material Gold

Contact Features

Center Contact Plating Material Gold

Center Contact Material Brass

Connector Product Type Connector Assembly

RF Connector Contact Configuration Not Captivated

Termination Features

Termination Method to Wire & Cable Solder/Clamp

Dimensions

Mated Outer Diameter (Approximate) 6.35 mm [.25 in]

Length 16.7 mm [.657 in]

Flats Dimension 8.0 A/F

Usage Conditions

Cable Type KX 22A, KX 3B, RG 174A, RG 188A, RG 316, URM 95

Packaging Features

Packaging Method Box

Packaging Quantity 100

Other

Dielectric Material PTFE

Gasket Material Silicone Rubber

Coupling Nut Plating Material Gold

Coupling Nut Material Stainless Steel

Grade Professional

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
