

PART NO.	MAX. BUNDLE DIA.	"L" LENGTH REF	"W" WIDTH REF.	"T" THICKNESS REF.	"A" REF	"B" REF	MIN. LOOP TENSILE
WITA-F1-18R-M	.87 (22)	3.98 (100)	.10 (2.5)	.039 (1)	1 (25.4)	.31 (7.9)	18 LBS.
WITA-F2-18R-M	.98 (25)	4.33 (110)					



WITA-F1-18R



WITA-F2-18R

NOTES:
1. MATERIAL: NYLON 6/6 (RMS-01).
2. COLOR: NATURAL.
3. MATERIAL: UV STABILIZED (RMS-46), COLOR: BLACK, AVAILABLE BY SPECIAL ORDER ONLY. TO ORDER ADD SUFFIX "-UVB" TO PART NO.
4. SUFFIX "-M" IS FOR PACKAGING OF 1000 PCS.

REV	DESCRIPTION	ENGR DATE
B	ADDED NOTE 4. SEE CO 200661	DK 05.12.11
A	RELEASED FOR PRODUCTION, CO 200524	DK 05.27.10

TITLE: MARKER FLAG TIES

DWG IN IN (mm)

TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°

FILE # WITA-F | DWN: D.K. | DT:05/27/10

MAT'L: SEE NOTES | CHKD:D.Z. | ENG:D.K.

RE: RICHCO, INC.

RICHCO INC.
ENG@RICHCO-INC.COM
(773) 539-4060

FINAL

PART # SEE TABLE

PRINT TYPE CA

Downloaded from Arrow.com.