

CATALOG LISTING

BFL1-BL1

PAGE 1 OF 1

REPLACES

RELEASE NO. 203802

CHECK

CHECK

06SEP01

SAV

CHECK

06SEP01

TRF

PTC/CAD 3D

DRAWN

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929



SWITCH-ENCLOSED

CATALOG LISTING

BFL1-BL1

NOTES

- 1 - 3X 6-32 UNC PRESSURE PLATE TERMINAL SCREWS
2 FURNISHED UNASSEMBLED
3 SWITCH WILL OPERATE AND RELEASE WITHIN THIS TRAVEL



ROLLER LEVER MAY BE POSITIVELY LOCKED AT INTERVALS OF APPROXIMATELY 0.2° WITHIN A RANGE OF 225° (1238 POSITIONS)

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH


CHARACTERISTICS
OPERATING FORCE38 OZ MAX
TOTAL TRAVEL3 .370 MIN
DIFFERENTIAL TRAVEL065 NOM

ELECTRICAL DATA
CONTACT ARRANGEMENT
S P D T

L156
11A 1/3HP 125, 250, 277 VAC
1/2A 125 VDC, 1/4A 250 VDC
4A 125 VAC "L"



THIRD ANGLE PROJECTION



SCALE	FULL
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.0) ±.030
TWO PLACE	(.00) ±.015
THREE PLACE	(.000) ±.005
ANGLES	±
WEIGHT	

ANSI Y14.5M-1982 APPLIES