Part Number : 1200170004
Product Description : Micro-Change (M12) to Nano-Change Snap Adapter, 3 Poles, 44.7mm Length
Series Number : 120017
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 853030



Documents and Resources

Drawings

1200170004_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

Downloaded from Arrow.com.

General

Status	Active
Category	Industrial Connectors
Series	120017
Description	Micro-Change (M12) to Nano-Change Snap Adapter, 3 Poles, 44.7mm Length
IP Rating	IP67
Product Name	Micro-Change (M12),Nano-Change (M8)
Type	In-Line Interconnect
UPC	883906144654

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	60V

Physical

Cable Diameter	N/A
Coupling Type	N/A
Gender	Female-Male
Keyway	Single
Material - Connector Body	PUR
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	8.080/g
Orientation	Straight
Poles	3
Temperature Range - Operating	-25° to +85°C
Wire Size (AWG)	N/A

Downloaded from Arrow.com.