



Part Number : [1300990167](#)
Product Description : MAX-LOC/Watertite Cord Grips, 1/2" NPT, Straight Male, Body Size F2, Cable Diameter 9.53-11.10mm (.375-.437")
Series Number : 130099
Status : Active
Product Category : Cable Grips
Engineering Number : 5631M


Documents & Resources

Drawings

[1300990167_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest



- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130099
Description	MAX-LOC/Watertite Cord Grips, 1/2" NPT, Straight Male, Body Size F2, Cable Diameter 9.53-11.10mm (.375-.437")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC,Watertite
Type	Strain Relief Grip
UPC	78678822650

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	9.53-11.10mm (.375-.437")
Color - Grommet	Green
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	Stainless Steel
Mesh Length	N/A
Number of Holes	1
O-Ring	N/A
Thread Size	1/2" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>
MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black	<u>1300990149</u>
MAX-LOC O-Ring, 1/2" NPT	<u>1301800314</u>

This document was generated on Sep 13, 2025