





NOTES:

1. MATERIAL AND FINISHES:
   CONTACT: PRECISION MACHINED COPPER ALLOY, 1.27µ [.000050] GOLD OVER COPPER PLATE.
   POSIBAND CLIP: BERYLLIUM COPPER, 1.27µ [.000050] GOLD PLATE.
2. DETAILED PRODUCT, MECHANICAL AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST HIGH PERFORMANCE D-SUB PRODUCT PUBLICATION AT CONNECTPOSITRONIC.COM.
3. CRIMPING TOOL INFORMATION IS AVAILABLE AT WWW.CONNECTPOSITRONIC.COM/CrimpToolCrosslist.
4. CONTACTS ARE COMPLIANT TO THE CURRENT RoHS DIRECTIVE.

BY: YBK	CHK: EB	3RD ANGLE	POSITRONIC BELIEVES THE DATA ON THE DRAWING TO BE RELIABLE. THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.
APR: PA	RELEASED DATE: 2020-07-24	SCALE: NTS	Positronic® CONNECTPOSITRONIC.COM
TOLERANCES: ±0.03mm [.001 INCHES]FOR MALE CONTACT MATING DIAMETERS ±0.08mm [.003 INCHES]FOR CONTACT TERMINATION DIAMETERS ±0.13mm [.005 INCHES]FOR ALL OTHER DIAMETERS ±0.38mm [.015 INCHES]FOR ALL OTHER DIMENSIONS ±5° FOR ALL ANGLES DIMENSION ARE IN MILLIMETERS [INCHES]		PART NUMBER: FC6020M2/AA	SERIES: SND
		TITLE: FC6020M2/AA	
		CREATED ON: 2020-07-17	SHEET: SHEET 1 OF 1 REV: A

Downloaded from Arrow.com.