



Part Number : [1300960050](#)

Product Description : Liquid-Tight Grip Strain Relief, 1/2" NPT, 90° Angle Male, Mesh Length 0.098m (3.875")

Series Number : 130096

Status : Active

Product Category : Cable Grips

Engineering Part Number : 36400



Documents and Resources

Drawings

[1300960050 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130096
Description	Liquid-Tight Grip Strain Relief, 1/2" NPT, 90° Angle Male, Mesh Length 0.098m (3.875")
NEMA Rating	NEMA 4
Product Name	Liquid-Tight
Type	Strain Relief Grip
UPC	78678836400

Agency

CSA	LR32159
UL	E61303

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	90° Angle
Cable Diameter	N/A
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Malleable Iron, Zinc Plated Steel
Material - Grip	Stainless Steel
Mesh Length	0.098m (3.875")
Net Weight	205.461/g
Number of Holes	N/A

O-Ring	N/A
Thread Size	1/2" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>
MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black	<u>1300990149</u>
MAX-LOC O-Ring, 1/2" NPT	<u>1301800314</u>

This document was generated on Apr 25, 2026