

Bosch Worldwide (http://www.bosch.com)
EN | DE (https://www.bosch-connectors.com/view/?p_p_auth=1&p_p_id=49&p_p_lifecycle=1&p_p_state=normal&p_p_mode=view&_49_struts_action=%2Fmy_sites%2Fview&_49_groupId=14301&_49_privateLayout=false)
Sn-2-5-4-mm%C2%B2/1928498652&_49_struts_action=%2Fmy_sites%2Fview&_49_groupId=14301&_49_privateLayout=false)
Login / Register

Bosch Connectors (https://www.bosch-connectors.com/view?
p_p_auth=1&p_p_id=49&p_p_lifecycle=1&p_p_state=normal&p_p_mode=view&_49_struts_action=%2Fmy_sites%2Fview&_49_groupId=14301&_49_privateLayout=false)
 **BOSCH** (https://www.bosch-connectors.com/view?
_auth=1&p_p_id=49&p_p_lifecycle=1&p_p_state=normal&p_p_mode=view&_49_struts_action=%2Fmy_sites%2Fview&_49_groupId=14301&_49_privateLayout=false)

Search for the products



1 928 498 652	
Status Active	Packaging Unit 1700 piece
Selected Technical Details	
Blade Width	4.8
Primary Locking (Terminal)	Lance-locking
Terminal Plating	tin-plated
Wire Cross Section	2.5 - 4 mm²
Full Technical Details	

Downloads	
Offer Drawing	https://ps-gsconnector-1928A00393-us.resource.bosch.com/media/1928A00393-DEEN%20AGZ%20001%2006%201%20%20SAP-Status%2040%20%20Labor%20F15%20%20Change%20F1928498652
Technical Customer Documentation	Login/Register to download
Processing Specification	Login/Register to download

Technical Data	
Manufacturer	Bosch
Packing Unit	1700 pc.
Gender	Female
Product Type	Terminal
Blade Width	4.8
Primary Locking (Terminal)	Lance-locking
Terminal Plating	tin-plated
Wire Cross Section	2.5 - 4 mm²
Wire Material	Copper
Row Distance	9 (8) mm
Line Voltage From	20 mV (DC)
Line Voltage To	40 V (DC)