51872-1 Product Details



Active

Ring and Spade Tongue Terminals

BODY,RING 16-14 6

51872-1

TE Internal Number: 51872-1

Product Highlights View All

- Terminal Shape = Ring Tongue
- Receptacle Style = Straight
- Body Style = SOLISTRAND
- Barrel Type = Closed Barrel
- Wire/Cable Type = Regular Wire

Pricing & Availability
Request Sample
Add to My Part List
Buy Product through Distributor

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Receptacle Style	Straight
Barrel Type	Closed Barrel
Wire/Cable Type	Regular Wire
Insulation	No
Insulation Support	Non-Insulation Support
Stud Size	10
Shape	RING-048
Heavy Duty	No
Finish	Tin

Termination Features

Wire/Cable Size (CMA)	2,050 – 5,180

Dimensions

Stud Diameter (mm [in])	5.00 [0.197]

Body Features

Body Style	SOLISTRAND
Wire Range (mm [AWG])	1.25-2.00² [16-14]
Material	Copper

Contact Features

Terminal Shape	Ring Tongue

Industry Standards

Government/Industry Qualification	No
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant

Packaging Features

Packaging Method	Loose Piece

Other

Brand	TE Connectivity

Related Products

Not quite the product you're looking for?
Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

Provide Website Feedback

Feedback

Downloaded from Arrow.com.