


OCA DIAGONAL: 13.18 [334.85]
VA DIAGONAL: 12.41 [315.14]
PA DIAGONAL: 11.72 [297.57]

TOP LEVEL NUMBER	US NUMBER	TYPE	DM "A" (TOTAL GLASS TO CONNECTOR)	A/G - FINISH	PROD SPEC
17-8571-203	98-0003-2629-2	FFC	4.27" [108.46]	AG500	23655
17-8571-221	98-0003-2632-6	SER	4.27" [108.46]	AG500	23655
17-8571-206	98-0003-2650-0	NOV	SEE DWG	AG500	23655
17-8571-218	98-0003-3273-8	USB R	4.27" [108.46]	AG500	23655



PINOUT
1 UL
2 UR
3 SHLD
4 LR
5 LL

REV	DATE	BY	CHK
J	4/13	SB	
G	2/12	SB	
G	9/11	SB	

NOTES:

1. WEIGHT OF GLASS IN GRAMS: 413±10%
2. NICOMATIC HOUSING P/N: OLO5
3. NICOMATIC RECEPTACLES (PINS) MATTE TIN PLATED P/N: 14106-12
4. HOUSING ORIENTED WITH LATCH DOWN

.147±.020 [3.73±.51]
TOTAL THICKNESS
OF GLASS CABLE
AND STRAIN RELIEF

UNITS	INCHES [MM]
TOLERANCES UNLESS SPECIFIED	
X .XX ±.03 [1.76]	
.XXX ±.015 [1.38]	
ANGLES ±1°	

MARKETING DRAWING
SCT32NN 12.41"

DO NOT SCALE DRAWING	SCALE
1 = 1	

REV	DATE	BY	CHK
J	4/13	SB	
G	2/12	SB	
G	9/11	SB	